


TABLE 1

CLASS	MATERIAL/FINISH
F	ALUMINIUM/NICKEL PLATED
K	STAINLESS STEEL/PASSIVATED
KE	STAINLESS STEEL/PASSIVATED
W	ALUMINIUM/OLIVE DRAB CADMIUM PLATED
Z	ALUMINIUM/ZINK NICKEL PLATED

TABLE 4

CABLE ENTRY SIZE CODE	AA +/-0,1	BB +/-0,1	CC +/-0,3	DD +0,2/-0
A	4,7	7,7	12,2	1,12
B	6,4	9,4	14,0	1,12
C	7,9	11,0	15,5	1,12
D	9,5	12,6	17,1	1,12
E	11,1	14,1	18,7	1,12
F	12,7	15,7	20,3	1,12
G	15,9	18,9	23,5	1,12
H	19,1	22,0	26,7	1,12
J	22,2	25,2	29,8	1,75
K	25,5	28,4	33,0	1,75
L	28,6	31,5	36,2	1,75
M	31,8	34,7	39,4	1,75

STAINLESS STEEL VERSION




TABLE 2

SHELL SIZE	A MAX	B MAX	C THREAD	D +0/-0,25	D2 +0/-0,25	E MAX	G MAX	H MAX	J MAX	I MIN	N	MAXIMUM ENTRY SIZE
08	22,48	15,67	1/2-20 UNF	6,86	6,68 see note 3	15,30	16,10	10,20	31,05	4,95	12	D
10	25,65	18,64	5/8-24 UNEF	9,53	9,35 see note 3	15,30	17,90	13,70	34,21	4,95	15	F
12	28,83	21,79	3/4-20 UNEF	12,98	12,62 see note 3	15,30	19,40	16,80	37,95	4,95	21	H
14	32,00	24,99	7/8-20 UNEF	14,86	14,86	15,30	20,00	17,90	39,65	4,95	24	J
16	35,18	28,24	1-20 UNEF	18,03	17,73 see note 3	15,30	21,60	21,20	41,25	4,95	30	K
18	38,55	30,94	1 1/16-18 UNEF	20,04	20,04	15,30	22,60	23,20	43,75	4,95	33	K
20	41,53	34,16	1 3/16-18 UNEF	23,22	23,22	15,30	24,10	26,20	46,91	4,95	36	L
22	44,70	37,29	1 5/16-18 UNEF	26,39	26,39	15,30	25,70	29,40	50,10	4,95	39	M
24	47,89	40,46	1 7/16-18 UNEF	29,31	29,31	15,30	27,40	32,60	53,29	4,95	42	M
28	54,23	49,45	1 3/4-18 UNS	35,28	35,28	15,30	30,90	39,60	56,46	4,95	54	M

* NOTES:

1 - MINIMUM PENETRATION OF ØD OR ØD2 FROM FRONT OF SERRATIONS
2 - PLEASE NOTE THERE MAY BE CROSSOVER DEPENDENT ON DIAMETER AND PITCH
3 - APPLY TOLERANCE +0,18/-0

EN3660-065W10B
- SERIES
- CLASS, MATERIAL FINISH (TABLE 1)
- SHELL SIZE (TABLE 2)
- CABLE ENTRY SIZE CODE (TABLE 4)

DRAWN	W.RUST	DATE 26/04/2018
SALES APPR	H.TAILLANDIER	26/04/2018
DESIGN APPR	M.PAUL	04/04/2014
PROD APPR	J.STEPHENSON	04/04/2014
QUAL APPR	P.REES	04/04/2014
ISSUE 3	CRN 26875	
NCAGE CODE U5792	WEIGHT	

3RD ANGLE PROJECTION NOT TO SCALE

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS IN MILLIMETRES
GENERAL TOL
LINEAR +/-0,25MM
ANGULAR +/- 3°

MATERIAL
SEE ABOVE
FINISH
SEE ABOVE

POLAMCO LTD
www.polamco.com
WESTON LOCK
LOWER BRISTOL ROAD
BATH BA2 1EP

THIS DRAWING IS COPYRIGHT AND THE PROPERTY OF POLAMCO LTD IT MUST NOT BE COPIED, USED FOR MANUFACTURE OR OTHERWISE DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF THE COMPANY.

ASSY USED ON: EN2997

TITLE: 90° ANTI-DECOUPLING BANDING ADAPTOR

PART NUMBER: EN3660-065****

DRAWING NO: P20030

SHT 1

Downloaded from Arrow.com.