



Part Number : [2260560244](#)
Product Description : Quad-Row Board-to-Board
Receptacle, 0.175mm Pitch, 0.60mm Mated Height,
2.00mm Mated Width, 24 Circuits, 2 Reels/Carton
Series Number : 226056
Status : Active
Product Category : Board-to-Board Connectors



Documents and Resources

Drawings

- [2260560244_sd.pdf](#)
- [2260560244_stp.zip](#)
- [2260560244.dxf](#)

Specifications

- [2260569200-SPK-201.pdf](#)
- [2260560000-PS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Board-to-Board Connectors
Series	226056
Description	Quad-Row Board-to-Board Receptacle, 0.175mm Pitch, 0.60mm Mated Height, 2.00mm Mated Width, 24 Circuits, 2 Reels/ Carton
Application	Board-to-Board
Component Type	Receptacle
Product Name	Quad-Row
UPC	198282702153

Electrical

Current - Maximum per Contact	0.3A, 4.0A
Voltage - Maximum	50V AC (RMS)/DC

Physical

Breakaway	No
Circuits (Loaded)	24
Circuits (maximum)	24
Color - Resin	Black
Durability (mating cycles max)	30
Glow-Wire Capable	No
Mated Height	0.60mm

Mated Width	2.00mm
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Liquid Crystal Polymer (LCP)
Net Weight	9.164/mg
Number of Rows	4
Orientation	Vertical
Packaging Type	Embossed Tape on Reel
PCB Locator	No
PCB Retention	Yes
Pitch - Mating Interface	0.175mm
Pitch - Termination Interface	0.35mm
Plating min - Mating	0.100µm
Plating min - Termination	0.050µm
Polarized to Mating Part	No
Polarized to PCB	No
Temperature Range - Operating	-40° to +85°C
Termination Interface Style	Surface Mount

Mates With / Use With

Mates with Part(s)

Description	Part Number
Quad-Row Board-to-Board Plugs	<u>226057</u>

This document was generated on Apr 30, 2026