

© 2022TE Connectivity. All Rights Reserved.


< TABLE I >


CONTACT	1.2mm MCON TERMINAL			APPLICATION SPEC.
P/N	1452653-1	1452656-1	1452659-1	114-18464
WIRE SIZE (mm2)	0.35	0.5~0.75	1.0	


CONTACT	2.8mm MCP TERMINAL			APPLICATION SPEC.
P/N	1-968880-1	1-968849-1	1-968851-1	114-18148
WIRE SIZE (mm2)	0.35~0.5	0.5 ~ 1.0	>1.0 ~ 2.5	











SECTION A-A

NOTES ;
1. GENERAL TOLERANCE : ±0.3mm, ±3°
2. RETAINER IS PRE-LOCKING
3. MATING CAP ASS'Y : X-2109455-X
4. APPLICABLE TERMINAL : SEE TABLE I


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED	22.NOV'12	DG	HG
	B	REVISED(ECR-22-159222)	15SEP2023	JY	KT


2	NATURAL	PBT	DBL HSG	1	1	1	1
1	GREEN	PBT-GF15	.050/.110 HYB 48P PLUG HSG Key code D	-	-	-	1
	BROWN	PBT-GF15	.050/.110 HYB 48P PLUG HSG Key code C	-	-	1	-
	GRAY	PBT-GF15	.050/.110 HYB 48P PLUG HSG Key code B	-	1	-	-
	BLACK	PBT-GF15	.050/.110 HYB 48P PLUG HSG Key code A	1	-	-	-
NO.	COLOR/FINISH	MATERIAL	DESCRIPTION	QTY			

DESCRIPTION	.060/.110 HYB 8P PLUG ASM CODE A	.060/.110 HYB 8P PLUG ASM CODE B	.060/.110 HYB 8P PLUG ASM CODE C	.060/.110 HYB 8P PLUG ASM CODE D
ASS'Y P/N	0-2109452-2	1-2109452-3	2-2109452-4	3-2109452-7


0-2109452-2 (KEY CODE A)
MATING CAP ASS'Y : 5-2109455-2




1-2109452-3 (KEY CODE B)
MATING CAP ASS'Y : 1-2109455-3



2-2109452-4 (KEY CODE C)
MATING CAP ASS'Y : 2-2109455-4



3-2109452-7 (KEY CODE D)
MATING CAP ASS'Y : 3-2109455-7



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±-
2 PLC ±-
3 PLC ±-
4 PLC ±-
ANGLES ±-

MATERIAL: SEE TABLE material_2

FINISH: - finish_spec_2

DWN: DG JEONG
CHK: KT LIM
APVD: HG CHO
PRODUCT SPEC: -
APPLICATION SPEC: SEE TABLE I
WEIGHT: -

TE Connectivity

NAME: .050/.110 HYB 48P PLUG ASS'Y

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-2109452	-

CUSTOMER DRAWING | SCALE 1:1 | SHEET 1 OF 1 | REV B

Downloaded from Arrow.com.