
THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
© COPYRIGHT ALL RIGHTS RESERVED.


LOC	DIST
H	-

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	F4	8-188431-6 ACTIVATED	20AUG2014	NV	JK




SCALE 3:1




PACKAGING/REELING DIRECTION




DETAIL A
SCALE 1:1



SECTION A-A





NOTES:


1 PACKAGING ACCORDING EIA-481/ DIN IEC 286

2 QUANTITY PER REEL 1200 PCS. REEL DIA. 380 MM


3 PN 9-188431-0 (20 POSITIONS) AS DRAWN.

4 3.0 - 5.0 µm TIN OVER 0.5 µm NICKEL PLATING.

5 PICK & PLACE AREA.



RECOMMENDED PC- BOARD PAD LAYOUT



SCALE 3:1

REMARK	PARTNUMBER	POS	" A"	"B" MAX	"C"	"D"	TAPE WIDTH(mm)
TOOLED	7-188431-4	4	2.54	7.1	3.81	7.78	24
TOOLED	7-188431-6	6	5.08	9.7	6.35	10.32	24
TOOLED	7-188431-8	8	7.62	12.2	8.89	12.86	24
TOOLED	8-188431-0	10	10.16	14.7	11.43	15.4	24
NOT YET TOOLED	8-188431-2	12	12.7	17.3	13.97	17.94	32
TOOLED	8-188431-4	14	15.24	19.8	16.51	20.48	32
TOOLED	8-188431-6	16	17.78	22.4	19.05	23.02	44
NOT YET TOOLED	8-188431-8	18	20.32	24.9	21.59	25.56	44
TOOLED	9-188431-0	20	22.86	27.5	24.13	28.10	44

ITEM NO.	COMPONENT DESCRIPTION	MATERIAL	FINISH
3	PICK & PLACE FEATURE	G.F POLYAMIDE. COLOR:BLACK	
2	FEMALE CONTACT	PHOSPHOR BRONZE	4
1	FEMALE HOUSING	G.F POLYAMIDE. COLOR:RED	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± 0.2
2 PLC	± -
3 PLC	± -
4 PLC	± -
ANGLES	± -

MATERIAL SEE TABLE

FINISH SEE TABLE

DWN	M.Gosselink 25/09/00
CHK	M.Gosselink -
APVD	- -
PRODUCT SPEC	108-19052
APPLICATION SPEC	114-13318
WEIGHT	-

TE Connectivity

NAME MICRO MATCH, FEMALE BOTTOM ENTRY SMD INBOARD CONNECTOR -

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3		C- 188431	

CUSTOMER DRAWING | SCALE 4:1 | SHEET 1 OF 1 | REV F4

1470-19 (3/11)

Downloaded from Arrow.com.