



**Part Number :** [1300980029](#)  
**Product Description :** MAX-LOC Strain Relief Cord-Sealing Grip, 3/8" NPT, Straight Male, Cable Diameter 4.75-6.35mm (.187-.250")  
**Series Number :** 130098  
**Status :** Active  
**Product Category :** Cable Grips  
**Engineering Number :** 5502



## Documents & Resources

**Drawings**  
[1300980029 sd.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Not Reviewed per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Cable Grips
Series	130098
Description	MAX-LOC Strain Relief Cord-Sealing Grip, 3/8" NPT, Straight Male, Cable Diameter 4.75-6.35mm (.187-.250")
NEMA Rating	NEMA 3R
Product Name	MAX-LOC
Type	Strain Relief Grip
UPC	78678872111

### Agency

CSA	LR32159
UL	E76954

### Physical

Approximate Break Strength	N/A
Bale Length	N/A
Body Style	Straight
Cable Diameter	4.75-6.35mm (.187-.250")
Color - Grommet	Orange
Eye Type	N/A
Gender	Male
Material - Body	Nylon
Material - Grip	N/A
Mesh Length	N/A
Net Weight	125.000/g
Number of Holes	1
O-Ring	No

Thread Size	3/8" NPT
-------------	----------

**Mates With / Use With**

**Use with Part(s)**

Description	Part Number
MAX-LOC Lock Nut 3/8" NPT	<u>1300990142</u>
MAX-LOC Gasket Sealing Ring, 3/8" NPT, Black	<u>1300990148</u>

---

This document was generated on Sep 24, 2025