Part Number: 11-27-5244

ANVIL 1560/1



Series image - Reference only

Status:	Active
Series:	J5872
Category:	Molex Parts
Engineering/Old PN:	J5872-001G

Go to **Part Detail**

CHECK DISTRIBUTOR INVENTORY

Add to My Parts

Note - Please disable browser pop-up blockers to view documents on www.molex.com

Product Environmental Compliance

EU ELV:Not Reviewed

EU RoHS:Not Reviewed

EU RoHS Phthalates:Not Reviewed

China RoHS:Not Reviewed

REACH SVHC:Not Reviewed

Low-Halogen Status:Not Reviewed

*Molex Product Compliance Declaration

Product Compliance Statement

EU RoHS Certificate of Compliance (PDF)

Multiple Part Product Compliance Statements
EU RoHS, REACH SVHC, & Low-Halogen

Multiple Part Industry Compliance Documents
*IPC 1752A Class C
*IPC 1752A Class D

Questions on Product Environmental Compliance? Email ProductCompliance@molex.com

Request Molex's CMRT from conflictminerals@molex.com

Application Tooling

FAQ

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling
Check our list of old tooling that used to be available for this part

Part Detail

VIEW ALL

- General
- Material Info

Downloaded from Arrow.com.

Molex is a registered trademark of Molex, LLC in the United States of America and may be registered in other countries; all other trademarks listed herein belong to their respective owners.

© Copyright 2017

Downloaded from Arrow.com.