

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories → Spacers

General Information

Extended Product Type:	ES-TC6
Product ID:	1SNK900105R0000
EAN:	3472599097285
Catalog Description:	ES-TC6 Spacer - Dark Grey
Long Description:	ES-TC6 Spacer - Dark Grey.

Ordering

Color:	Dark Grey
Minimum Order Quantity:	10 piece
Customs Tariff Number:	39269097

Popular Downloads

Data Sheet, Technical Information:	1SNK160042D0201
Instructions and Manuals:	1SNK160027C0201

Dimensions

Product Net Width:	0.8 mm
Product Net Height:	34.2 mm
Product Net Length:	42.5 mm
Product Net Depth / Length:	42.5 mm
Product Net Weight:	0.8 g

Technical

Spacing:	0.8 mm
Function:	Spacers
Pollution Degree:	3
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polyamide
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715 TH15-5.5 (15 x 5.5 mm Mounting Rail) acc. to IEC 60715

Suitable For: TC5
ZDK4-22
ZDS4-22-R1
ZK2.5-SF
ZK2.5-SF-R
ZK2.5-S-R1
ZK4
ZK4-3P
ZK4-4P
ZK4-PE
ZK4-PE-3P
ZK4-PE-4P
ZS4-PE-R2
ZS4-R2
ZS4-SF
ZS4-SF-R
ZS4-SF-T
ZS4-SP-R1
ZS4-SP-T2-R1
ZS4-S-R1
ZS4-S-R2
ZS4-S-T-R1
ZS6
ZS6-3S
ZS6-3S-PE
ZS6-4S
ZS6-4S-PE
ZS6-D1
ZS6-D1-PE
ZS6-D2

Technical UL/CSA

Flammability According to UL94: V0

Environmental

Ambient Air Temperature: Operation -55 ... +110 °C
Storage -55 ... +110 °C

Resistance to Vibrations acc. to IEC 60068-2-6: Compliant

RoHS Status: Following EU Directive 2002/95/EC August 18, 2005 and amendment

Certificates and Declarations (Document Number)

Environmental Information: 1SND220088E1000

Instructions and Manuals: 1SNK160027C0201

RoHS Information: 1SND230503F0202

Classifications

Object Classification Code: X

E-nummer: 2925152

Container Information

Package Level 1 Units: 10 piece

Package Level 1 Width: 85 mm

Package Level 1 Depth / Length: 100 mm

Package Level 1 Height: 5 mm

Package Level 1 Gross Weight: 0.008 kg

Package Level 1 EAN: 3472599097285

Package Level 2 Units: 2000 piece

Package Level 2 Width: 200 mm

Package Level 2 Depth / Length: 300 mm

Package Level 2 Height: 200 mm

Product Packing Type: Bag

