




APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	8/14/18	
A		UPDATE DRAWING	3/4/19	AY/KC




TERM 1	DATA 2
TERM 2	CD/DATA 3
TERM 3	CMD
TERM 4	VDD
TERM 5	CLK
TERM 6	VSS
TERM 7	DATA 0
TERM 8	DATA 1

RECOMMENDED
PCB PATTERN LAYOUT(TOP VIEW)
TOLERANCE: ±0.05

▨ SOLDERPROHIBITED AREA
▨ PATTERN PROHIBITED AREA
■ PROHIBITED AREA

SPECIFICATIONS:
Material:
Housing: Hi-Temp Thermoplastic, rated UL 94V-0
Slider: Hi-Temp Thermoplastic, rated UL 94V-0
Terminal: Copper Alloy
Shell: Stainless Steel, Nickel plated, Gold on Solder area
Plating:
Gold Flash over Nickel underplate on contact area,
Matte Tin over Nickel underplate on Solder tails
Electrical:
Voltage rating: 100 VAC/DC rms
Current rating: 0.5 A
Contact resistance: 100 mohms max
Insulation resistance: 1000 Mohms min @ 250 VDC
Dielectric withstanding voltage: 500 VAC for 1 minute
Temperature Rating:
Operating temperature: -25°C to +85°C
Environmental:
Lead free, RoHS compliant.



PACKAGED ON TAPE & REEL

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MILLIMETERS TOLERANCES: EXCEPT AS NOTED MM ANGLE .X ± 0.25 X. ± 5° .XX ± 0.15 X.X ± 2° X.XX ± 1°		ADAM TECH INTERCONNECTS 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
APPROVALS		TITLE	
DRAWN	AY	MICRO SD (T-FLASH) PUSH PUSH TYPE 1.45H CONNECTOR	
CHECKED	DH	SIZE X PART NO. MCSP-L1-08-A-SG-T/R	
APPROVED		REV. A	
		REF: S00226T	SCALE: NTS
		SHEET 1 OF 1	

