



Extended length is with 500g of force



P1		P2
1	WHITE	1
2	BLACK	2
3	RED	3
4	GREEN	4
5	YELLOW	5
6	BLUE	6

Extended Length ("L2")	Typical Retracted Length ("L1")
168.0 Inches - 193.2 Inches	53.5 Inches
4,267.2MM-4,907.28MM	1,358.9MM

SBC: A=A

Material:

- Plug Housing: Polycarbonate, clear
- Plug Terminal: 0.36"[0.14MM] Thick Phosphor Bronze
- Connector: 50μ" of Selective Gold Contact Plating
 - Area, Gold flash over the remainder
 - Over 2.54μm[.000100] thick nickel underplate
- Conductor(X6C): 26AWG (0.12X12) Bare Copper
- Insulation(X6C): PP6331 ID 0.95-1.0
- Jack: PVC No UL 80 P
- Package: Individual PE Bag

Scale	1:1							Name
TOLERANCE						Drawn	11.02.11	Chappel
X.X	±0.40					Approved		
X.XX	±0.25							
X.XXX	±0.15							
Angle	±3°							
								
			Modification	Date	Name			

Item No.	
----------	--

AT-C-26-6/6/S-14/R

	Title
--	-------

NON-UL 26 AWG (0.12X12)*6C, O.D.: 2.4*6.8MM,
Reverse Plug, 50μ" of contact plating, SILVER

Drawing No.

rev00

Replace

Sheet

RoHS
Complaint

ASSMANN
WSW/ components