



**Part Number :** [10013046](#)  
**Product Description :** 5.08mm Pitch SPOX Crimp Terminal Housing, 4 Circuits, Natural  
**Series Number :** 5197  
**Status :** Active  
**Product Category :** Connector Housings  
**Engineering Part Number :** 5197-04

---

## Documents and Resources

### Drawings

[010013046\\_sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)


### Specifications

[PS-5197-001-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

## Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Connector Housings
Series	5197
Description	5.08mm Pitch SPOX Crimp Terminal Housing, 4 Circuits, Natural
Application	Signal, Wire-to-Board
Product Name	SPOX
UPC	800754313131

### Agency

CSA	LR19980
UL	E29179

### Physical

Circuits (maximum)	4
Color - Resin	Natural
Flammability	94V-2
Gender	Receptacle
Glow-Wire Capable	No
Material - Resin	Nylon
Net Weight	1535.800/mg
Number of Rows	1

Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	5.08mm
Stackable	No
Temperature Range - Operating	-40° to +105°C

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
SPOX 5.08mm Pitch Vertical Single Row Headers	<u>5281</u>

### Use with Part(s)

Description	Part Number
SPOX Female Crimp Terminals	<u>5194</u>

---

This document was generated on Apr 29, 2026