

 Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



Converted to EU RoHS/ELV Compliant (Statement of Compliance)

- Wire Pin
- Without Insulation Support
- Wire/Cable Type = Regular Wire
- Wire Range = 0.75-1.00² [18.5-17]
mm [AWG]
- Brass Material

[Check Pricing & Availability](#)
[Search for Tooling](#)
[Product Feature Selector](#)
[Contact Us About This Product](#)

- Brand = AMP