Product Line

- DeepTronica
- Single Pair Ethernet
- ZConnect
- Ceres
- X-Lok
  - Accessory
  - Middle Size
  - Mini Size
  - Large Size
  - Standard Size
- M Series
- FLOS & FLOS+
- Power
- RBL
- HS-Lok
- NMEA 2000
- Heavy Duty Shielded
- RJ
- USB
- SSL
- HDMI
- DVI
- Fiber Optic
- RF
- Cable Joiner
- Cable Gland
- Pressure Relief Vent
- LED Light Guide
- D-Sub





CB-05AFMM-QL8D02

- Operating Temperature: -20°C ~ +80°C
- Transmission Speed: N/A
- Shielded: Plastic, Non-shielded
- Jacket Material: PVC
- Certificate: UL2238, UL50e

You must login first for view the price

Quantity − 1 +

Add to Cart | Inquiry

Can't find? Customize your part

Mating Pair & Accessories

Connector Type

Search



X-Lok, Middle Siz...
AB-CB05FL-CBHL...
-20°C ~ +80°C
− 0 +



X-Lok, Middle Siz...
AB-CB05FL-CBHL...
-20°C ~ +80°C
− 0 +



X-Lok, Middle Siz...
AB-CB05FL-CBHL...
-20°C ~ +80°C
− 0 +



X-Lok, Middle Siz...
AB-CB05FL-CBHL...
-20°C ~ +80°C
− 0 +



X-Lok, Middle Siz...
AB-CB05FL-CBHL...
-20°C ~ +80°C
− 0 +



X-Lok, Middle Siz...
AB-CB05FL-CBHL...
-20°C ~ +80°C
− 0 +

Add to Cart | Inquiry

Specifications | Download / CAD

Nominal Current **10A**	Connector Type **Overmolded**
Shielded **Plastic, Non-shielded**	No. of Contacts **05**
Connector Gender **Female**	Backshell **Straight**
Mating Style **Push Lock**	IP Rating **IP68**
Assembly Style **N/A**	

More Options

People Also Bought



CB-05AFMM-QL8D02



M12B05FL-12BMR-...



BD-05BFFA-QL8AN0



ACB-05AFFM-SL7A04



CB-03AMMM-RR7A01

Downloaded from Arrow.com.