



Part Number : [5035481822](#)

Product Description : SlimStack Board-to-Board Receptacle, 0.40mm Pitch, HRF (High Retention Force) Series, 0.70mm Mated Height, 2.60 Mated Width, 18 Circuits

Series Number : 503548

Status : Active

Product Category : Board-to-Board Connectors



Documents and Resources

Drawings

[5035481822 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)


[5035481822.dxf](#)

Specifications

[5035480003-PS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 33
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Board-to-Board Connectors
Series	0.4, HRF 7S
Description	SlimStack Board-to-Board Receptacle, 0.40mm Pitch, HRF (High Retention Force) Series, 0.70mm Mated Height, 2.60 Mated Width, 18 Circuits
Application	Board-to-Board
Component Type	Receptacle
Product Name	SlimStack
UPC	191128129664

Electrical

Current - Maximum per Contact	0.3A
Voltage - Maximum	50V AC/DC

Physical

Circuits (Loaded)	18
Circuits (maximum)	18
Color - Resin	Black

Durability (mating cycles max)	30
Glow-Wire Capable	No
Lock to Mating Part	Yes
Mated Height	0.70mm
Mated Width	2.60mm
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Net Weight	14.180/mg
Number of Rows	2
Orientation	Vertical
Packaging Type	Embossed Tape on Reel
PCB Locator	No
PCB Retention	Yes
Pitch - Mating Interface	0.40mm
Pitch - Termination Interface	0.40mm
Polarized to Mating Part	No
Polarized to PCB	No
Temperature Range - Operating	-40° to +85°C
Termination Interface Style	Surface Mount

Mates With / Use With

Mates with Part(s)

Description	Part Number
0.40mm Pitch SlimStack Board-to-Board Plugs	<u>503552</u>

This document was generated on Jun 02, 2026