



Part Number : [936010410](#)

Product Description : Heavy-Duty Turned Crimp Contact for 40A Inserts and Modules, Female, Silver (Ag) Plated Copper Alloy, 4.00mm² (12 AWG), 100 per Bag

Series Number : 93601

Status : Active

Product Category : Heavy-Duty Contacts

Engineering Part Number : 7600.5702.0



Documents and Resources

Drawings

[936010410_sd.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)


[Creo](#)

Specifications

[936010406-S00.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC

- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

Status	Active
Category	Contacts
Series	93601
Description	Heavy-Duty Turned Crimp Contact for 40A Inserts and Modules, Female, Silver (Ag) Plated Copper Alloy, 4.00mm ² (12 AWG), 100 per Bag
Contact Type	Turned Crimp
Product Name	Heavy-Duty Connectors
UPC	887191888682

Agency

CSA	256883
UL	E249674

Electrical

Current - Maximum per Contact	40.0A
-------------------------------	-------

Physical

Gender	Female
--------	--------

Material - Contact	Copper Alloy
Material - Plating	Silver
Net Weight	2.190/g
Number of Grooves	0
Packaging Type	Bag
Stripping Length	9.60mm
Wire Size (AWG)	12
Wire Size mm ²	4.00

Mates With / Use With

Mates with Part(s)

Description	Part Number
Heavy-Duty Connectors and Accessories	<u>93601</u>

Use with Part(s)

Description	Part Number
Use With	S-K, S-Q, S-QD, and S-M Inserts

This document was generated on Apr 23, 2026