

SAFFB2G59AA1F0A

In Production**Recommended****RoHS**

Note: This datasheet may be out of date.

Please download the latest datasheet of SAFFB2G59AA1F0A from the official website of Murata Manufacturing Co., Ltd.

<http://www.murata.com/en/products/productdetail?partno=SAFFB2G59AA1F0A>

Applications

Unsuitable Applications	Please be sure to read and comply with these "Precautions for use."
Specific Applications	Consumer equipment, Industrial Equipment Please refer to Our Website and specifications, etc. for information about the performance, functions, quality, management, and safety required for the above applications, and use Products after confirming the performance and reliability of the actual Product.
Recommended Applications	Consumer equipment



Packaging Information

Packaging	Specifications	Standard Packing Quantity
B0S	Sample Cut Tape or Bulk (1~99pcs)	0
R1S	Sample Embossed Tape & Reel (100pcs~)	0
R1X	180mm Embossed Tape	10000

1 of 2

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, its specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

SAFFB2G59AA1F0A



Specifications

Function	Rx Filters
Band	Band41
Size	1.1x0.9x0.5(max.)mm
Termination Impedance	Unbalanced

2 of 2

Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, its specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.