

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -
© COPYRIGHT copyright_date BY - TE ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	RIB CHANGED OF HOUSING	10APR2017	T.D	I.Y
	B1	PANEL SEAL OPTIMIZATION	25OCT2017	T.D	E.J
	C	ECR-20-000096	20MAY2020	J.L	I.Y
	C1	ECR-20-014384	27OCT2020	J.L	J.Z





Notes


1. PACKAGING: POSITION WAY IN CARDBOX
2. SUITABLE CONNECTOR SEE DRAWING: 2298567
3. SUITABLE RETAINER P/N; 2298573-1,2298574-1
4. SUITABLE CONTACT SEE TABLE
5. APPLICABLE PANEL SIZE
6. APPLICABLE PANEL THICKNESS: 0.65~0.7MM
7. FREE SAPACER FOR HARNESS CONNECTOR MOUNTING

C1


4 SUITABLE CONTACT

CONTACT	WIRE SIZE (mm^2)	PART NO.	REMARK
TAB 0.63	0.08-0.22	1355719	SEE DRAWING 929453
	0.13/0.17	2141828	
	0.25-0.35	928918	
	0.50-0.75	963716	
	0.22-0.35	2297494-1	SEE DRAWING 2327063
	0.50-0.75	2293362-1	
TAB 1.2	0.25-0.35	1718348	SEE DRAWING 1718398
	0.50-0.75	1718350	
	0.22-0.35	2294463-1	SEE DRAWING 2294463
	0.50-0.75	2294463-2	
	1.0-1.5	2294463-3	
TAB 2.8x0.8	0.20-0.50	964292	SEE DRAWING 1355364
	0.35	2141874	
	0.50-1.0	964294	
	>1.0-2.5	964296	

APPLICABLE PANEL SIZE 5 6



FREE SPACE FOR CONNECTOR MOUNTING 7



ASSY-PART-NO	CODE	COLOR	MATERMIAL	DESCRIPTION	ITEM
2298566-1	A	BLACK	EPDM	RUBBER, PANEL	2
		BLACK	PBT	22PSON.,TAB HSG.	1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED: ACC. TO DIN 16901-140
0 PLC ±
1 PLC ±0.1
2 PLC ±0.01
3 PLC ±0.001
4 PLC ±0.0001
ANGLES ±

MATERIAL SEE TABLE -

FINISH - -

PRODUCT CHARACTERISTICS ACC. QMP EMEA_12
BESONDERE MERKMALE NACH QMP EMEA_12

DWN J.ZONG 21-Jan-16
CHK S.W ANG 21-Jan-16
APVD -
PRODUCT SPEC -
APPLICATION SPEC -
WEIGHT -

TE Connectivity

NAME 22POSN.,TAB SIDE, HSG ASY MCP2.8K, MCON 1.2CB, MQS 0.64 -

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-2298566	

CUSTOMER DRAWING | SCALE 1:1 | SHEET 1 OF 1 | REV C1

1471-9 (3/13)

Downloaded from Arrow.com.