



**Part Number :** 02067103  
**Product Description :** 1.57mm Diameter,  
Standard .062" Pin and Socket PC Tail  
Terminal, Series 1779, Female, with 2.54µm  
Tin (Sn) Plated Brass Contact, Bag Packaged  
**Series Number :** 1779  
**Status :** Active  
**Product Category :** Crimp Terminals  
**Engineering Number :** 1779-(P909)L




Documents & Resources

Drawings  
[002067103\\_sd.pdf](#)  
[PK-1190-003-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

## Part Details

### General

Status	Active
Category	Crimp Terminals
Series	1779
Description	1.57mm Diameter, Standard .062" Pin and Socket PC Tail Terminal, Series 1779, Female, with 2.54µm Tin (Sn) Plated Brass Contact, Bag Packaged
Application	Power, Wire-to-Wire
Comments	PC Tail Brass for Standard .062" Housing
Product Name	Standard .062"
UPC	800753618404

### Physical

Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.160/g
Packaging Type	Bag
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	3.00mm max.
Wire Size (AWG)	N/A
Wire Size mm <sup>2</sup>	N/A

---

## Application Tooling

### Global

Description	Part Number
-------------	-------------

Extraction Tool for Standard .062" and Standard .062"+ Pin and Socket Terminals	<u>11030002</u>
---	-----------------

---

This document was generated on Apr 22, 2025