Part Number : 2318833022
Product Description : Pico-Lock Female-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, 3.00mm Pitch, Single Row, Gold (Au) Plating, 300.00mm Length, 16 AWG, 2 Circuits, Black
Series Number : 231883
Status : Active
Product Category : Power and Signal Cable Assemblies



Documents and Resources

Drawings

2318833022_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	231883
Description	Pico-Lock Female-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, 3.00mm Pitch, Single Row, Gold (Au) Plating, 300.00mm Length, 16 AWG, 2 Circuits, Black
Application	Wire-to-Board
Assembly Configuration	Single Ended Connector
Connector to Connector	Pico-Lock-to-Pigtail
Keyword	Pico-Lock 3.0
Product Name	Pico-Lock
Type	Discrete Wire Assembly
UPC	198930920410

Electrical

Current - Maximum per Contact	10.0A
Voltage - Maximum	250V AC (RMS)/DC

Physical

Cable Length	300.00mm
Circuits (Loaded)	2
Circuits (maximum)	2
Color - Resin	Black
Gender	Female-Pigtail
Lock to Mating Part	Yes
Material - Metal	Copper Alloy

Downloaded from Arrow.com.

Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Polybutylene Terephthalate (PBT)
Net Weight	11.220/g
Number of Rows	1
Overmolded	No
Packaging Type	Bag
Pitch - Mating Interface	3.00mm
Plating min - Mating	0.100µm
Plating min - Termination	1.000µm
Single Ended	Yes
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 1007
Wire Size (AWG)	16

Mates With / Use With

Mates with Part(s)

Description	Part Number
3.00mm Pitch, Pico-Lock Single Row, Right-Angle, Surface Mount PCB Headers	221115

Use with Part(s)

Description	Part Number
3.00mm Pitch, Pico-Lock Female Crimp Terminals	221113

Downloaded from Arrow.com.