



**Part Number :** [5055650801](#)


**Product Description :** 1.25mm Pitch, Micro-Lock Plus Receptacle Crimp Housing, Single Row, Positive Lock, 8 Circuits, Black

**Series Number :** 505565

**Status :** Active

**Product Category :** Connector Housings

---



## Documents and Resources

### Drawings

[5055650801\\_sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[5055650801.dxf](#)

### Specifications

[5055650000-AS-000.pdf](#)

[5055659200-200.pdf](#)

[5055650000-000.pdf](#)

[5055650003-PS-000.pdf](#)

[5055651000-PS-000.pdf](#)


[5055650002-000.pdf](#)

[5055651002-PS-000.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC

	61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

### Additional Product Compliance Information

## Part Details

### General

Status	Active
Category	Connector Housings
Series	505565
Description	1.25mm Pitch, Micro-Lock Plus Receptacle Crimp Housing, Single Row, Positive Lock, 8 Circuits, Black
Application	Signal, Wire-to-Board, Wire-to-Wire
Keyword	Micro-Lock Plus 1.25
Product Name	Micro-Lock Plus
UPC	889056531993

### Agency

UL	E29179
----	--------

## Physical

Circuits (maximum)	8
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	No
Lock to Mating Part	Yes
Material - Resin	Polybutylene Terephthalate (PBT)
Net Weight	165.344/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	1.25mm
Pitch - Termination Interface	1.25mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
1.25mm Pitch Micro-Lock Plus Vertical, Single Row, Surface Mount Headers	<u>505568</u>
1.25mm Pitch Micro-Lock Plus Right-Angle, Single Row, Surface Mount Headers	<u>505567</u>

### Use with Part(s)

Description	Part Number
Pre-Crimped Lead Micro-Lock Plus 1.25 Female-to-Micro-Lock Plus 1.25 Female, Matte Tin (Sn) Plating, 150.00mm Length, 26 AWG, Black	<u>797581148</u>
Pre-Crimped Lead Micro-Lock Plus 1.25 Female-to-Micro-Lock	<u>797581149</u>

Plus 1.25 Female, Matte Tin (Sn) Plating, 300.00mm Length, 26 AWG, Black	
Pre-Crimped Lead Micro-Lock Plus 1.25 Female-to-Micro-Lock Plus 1.25 Female, 0.10µm Gold (Au) Plating, 150.00mm Length, 26 AWG, Black	<u>797582143</u>
Pre-Crimped Lead Micro-Lock Plus 1.25 Female-to-Micro-Lock Plus 1.25 Female, 0.10µm Gold (Au) Plating, 300.00mm Length, 26 AWG, Black	<u>797582144</u>
1.25mm Pitch Micro-Lock Plus Female Crimp Terminals	<u>505431</u>

---

This document was generated on May 09, 2026