Part Number : 1200698539
Product Description : Micro-Change (M12) Single-Ended Cordset with Knurled Hexnut, 5 Poles, A-Coded, Female (Straight) to Pigtail, 22 AWG, Shielded Black WSOR Cable, 10.0m (32.81') Length
Series Number : 120069
Status : Active
Product Category : Circular Industrial Cordsets
Engineering Part Number : 805S00BS1M100



Documents and Resources

Drawings

1200698539_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 3; 47; 34; 33
China RoHS	Not Relevant
EU ELV	Not Reviewed per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Downloaded from Arrow.com.

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120069
Description	Micro-Change (M12) Single-Ended Cordset with Knurled Hexnut, 5 Poles, A-Coded, Female (Straight) to Pigtail, 22 AWG, Shielded Black WSOR Cable, 10.0m (32.81') Length
IP Rating	IP67
Product Name	Micro-Change (M12)
Protocol	N/A
Type	Single Ended
UPC	887191906911

Agency

UL	E152210

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	60V

Physical

Cable Diameter	6.10mm (.240")
Cable Length	10.0m (32.81')
Color - Cable Jacket	Black

Downloaded from Arrow.com.

Connector End A	Micro-Change (M12)
Connector End B	Pigtail
Coupling Style	Knurled Hexnut, Threaded
Gender	Female-Pigtail
Keyway	A-Coded
LED Indicator	None
Material - Cable Jacket	TPU
Material - Connector Body	TPU
Material - Contact	Brass
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	39.420/g
Orientation	Straight to Pigtail
Poles	5
Temperature Range - Operating	-25° to +85°C
Wire/Cable Type	UL 21215, Shielded TPU
Wire Size (AWG)	22

Downloaded from Arrow.com.