


[Enlarge](#)

BU-32601-* **Insulated Banana Coupler**

- IEC 1010 compliant
- 1000V, 15 Amp
- 4mm shrouded/unshrouded banana plugs accepted both ends
- Stainless steel tip (20 Amp)
- Mates w/ all shrouded, unshrouded & retractable 4mm banana plugs
- [Product Data Sheet](#)
- [Send us your questions about this product](#)

BU-26103-* **Insulated Plug-on Test Prod with Cage Spring - 1000V**

- Accepts all standard 4mm banana plugs
- Nine-leaf banana spring enters jacks w/ .750" (9mm) depth
- 4.35" length (115mm)
- Heat resistant silicone insulation
- 1000V category III
- IEC 1010 compliant
- Mates w/ all shrouded, unshrouded & retractable 4mm banana plugs
- [Product Data Sheet](#)
- [Send us your questions about this product](#)


[Enlarge](#)

[Enlarge](#)

Econo Safety Test Lead Shrouded Right Angle Banana Plug to Safety Test Prod **BU-4162-M-48-*** Silicone **BU-4162-N-48-*** PVC

- 1000V, 3 Amp
- BeCu contact hook & probe tip with retracted plunger
- Hook extends 0.41" (10mm) - fully insulated
- Insulated body with safety shock guard collar
- Slim-line prod design with clear kynar®
- Mech. connections: 0.16" (4mm) nickel-insulated right angle jack
- Mates w/ shrouded, unshrouded & retractable 4mm banana plugs
- IEC 1010 compliant
- [Product Data Sheet](#)
- [Send us your questions about this product](#)

BU-4591-M-47-* **Test Prod with Cage Spring to Shrouded Banana Plug Silicone**

- Fully insulated test lead mates w/ standard shrouded banana jack
- 17 AWG silicone insulated wire
- 1000V, category III; 1500V, category II
- 20 Amp
- [Product Data Sheet](#)
- [Send us your questions about this product](#)


[Enlarge](#)

*** represents color: 0=Black 2=Red 4=Yellow 5=Green 6=Blue 9=White**

[Up](#) | [Test Leads](#) | [Accessories](#) | [Oscilloscope Probes](#) | [Kits](#)

© 2003 Mueller Electric Company. All rights reserved.
Problems with the site should be reported to the [webmaster](#).