



**Part Number :** [1300088079](#)

**Product Description :** Mini-Change C-Size Single-Ended Cordset, 19 Poles, Female (Straight) to Pigtail, 22-19 AWG, Black TPU Cable, 5.0m (16.40') Length

**Series Number :** 130008

**Status :** Active

**Product Category :** Circular Industrial Cordsets

**Engineering Part Number :** 303000B80M050



---

## Documents and Resources

### Drawings

[1300088079 sd.pdf](#)

---

## Product Environment Compliance

### Compliance

|                    |  |
|--------------------|--|
| GADSL/IMDS         | Not Relevant                                   |
| China RoHS         | Not Relevant                                   |
| EU ELV             | Not Relevant                                   |
| Low-Halogen Status | Not Relevant                                   |
| REACH SVHC         | Contains Lead per D(2020)9139-DC (19 Jan 2021) |
| EU RoHS            | Compliant with Exemption 6(c) per EU 2015/863  |

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

## UKCA - Declaration of Conformity

## CE - Declaration of Conformity

---

## Part Details

### General

|              |   |
|--------------|---|
| Status       | Active  |
| Category     | Circular Industrial Cordsets  |
| Series       | 130008  |
| Description  | Mini-Change C-Size Single-Ended Cordset, 19 Poles, Female (Straight) to Pigtail, 22-19 AWG, Black TPU Cable, 5.0m (16.40') Length |
| IP Rating    | IP67  |
| Product Name | Mini-Change   |
| Type         | Single Ended  |
| UPC          | 889056891035  |

### Electrical

|                               |      |
|-------------------------------|------|
| Current - Maximum per Contact | 2.0A |
| Voltage - Maximum             | 300V |

### Physical

|                      |                 |
|----------------------|-----------------|
| Cable Diameter       | 10.20mm (.402") |
| Cable Length         | 5.0m (16.40')   |
| Color - Cable Jacket | Black           |
| Connector End A      | Mini-Change     |
| Connector End B      | Pigtail         |
| Coupling Style       | Threaded        |
| Gender               | Female-Pigtail  |
| Keyway               | Single          |
| LED Indicator        | None            |

|                               |                     |
|-------------------------------|---------------------|
| Material - Cable Jacket       | TPU                 |
| Material - Connector Body     | TPE                 |
| Material - Contact            | Copper Alloy        |
| Material - Coupling Nut       | Zinc Die-Cast       |
| Material - Plating Mating     | Gold                |
| Net Weight                    | 798.700/g           |
| Orientation                   | Straight to Pigtail |
| Poles                         | 19                  |
| Temperature Range - Operating | -40° to +90°C       |
| Wire/Cable Type               | UL 21215            |
| Wire Size (AWG)               | 19, 22              |

---

This document was generated on May 06, 2026