



Pushing Performance



# Han-Yellock 10 Kit, 3+PE screw, angled



Connector sets, Screw termination, Contacts: 3, Hood, Bulkhead mounted housing, Size: Han-Yellock® 10, Side entry, 1x M20

Part number: **10 22 003 0002**

## Technical data

Go to:

[Identification](#) [Version](#) [Technical characteristics](#) [Material properties](#) [Commercial data](#)

### Identification

Category	Connector sets
Series	Han-Yellock®
Type of hood/housing	Hood
	Bulkhead mounted housing

### Version

Termination method	Screw termination
Size	Han-Yellock® 10
Number of contacts	3
PE contact	Yes
Version	Side entry
Cable entry	1x M20

## Technical characteristics

Clamping range

6 ... 12 mm

## Material properties

RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

## Commercial data

Packaging size	1
Net weight	451 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27440101 Rectangular connectors (set)

### eShop

You can go directly to the shop here, and get detailed information about all HARTING products.

### Distributors

You can find all global distributors of HARTING products here.

### Contact

You can ask us questions about products and solutions or give feedback about our website here.

**HARTING Newsletter**

Your E-Mail Address

**Go to Registration form**

© HARTING TECHNIK GMBH & CO. KG. WE USE COOKIES TO OPTIMIZE THE DESIGN OF OUR WEBSITE, FOR CONTINUOUS IMPROVEMENT AND TO PROVIDE YOU WITH PERSONALIZED CONTENT AS WELL AS TECHNICAL INNOVATIONS THAT SUIT YOUR INDIVIDUAL INTERESTS. YOU WILL FIND FURTHER INFORMATION IN OUR [PRIVACY POLICY](#) AND IN OUR [IMPRINT](#).

Understood

