


[Home](#) > [Search Tools](#) > [Part Number](#)

Part Number Search

 You Searched For:

Note: Data provided here are offered in good faith and are as reliable and accurate as possible. However, they do not form part of any contract of supply or purchase unless specifically confirmed in writing by an authorized representative of ITT. All information and images shown are the property of ITT ICS and are not to be reproduced in any form without direct authorization from ITT ICS.

ITT ICS strongly recommends that you contact your local ITT Sales Office for confirmation of all the details you obtain through these Web pages. Please be aware that data may change at any time and without notice. For a listing of Sales Offices, local sales support, and authorized distributors please use the "Global Sales Locator" located either to the right of this data or at the top of every page.

-
-
-

Our Descriptive Part Number: 0758505000
 Our Global Manufacturing Part Number: 075-8505-000

<input checked="" type="checkbox"/>	YES	RoHS compliant =	material restrictions of lead, cadmium, hexavalent chromium, mercury, poly bromated biphenyl ether (PBB) and poly bromide diphenyl ether (PBDE) according to directive 2002/95/EC
<input type="checkbox"/>	NO	RoHS compatible =	Compatible with lead free soldering process

Product Datasheet	
Product Group	VG/CA-Bayonet
Component	Gasket
Shell Size	18
Type of Accessory	Gasket
Size of Cavity	18
Mounting Type	Rear
Electrically Conductive	No
Material	Polychloroprene (1,0 mm)
Dimension D1	Ø30,80 +1,00 (1.212 +.039)
Dimension D2	Ø4,20 +0,50 (.165 +.020)
Dimension E	27,00 ±0,20 (1.063 ±.008)
Dimension L	35,00 ±0,50 (1.378 ±.020)
Footnote	Dimensions are shown in mm (inch). Dimensions subject to change.
For more information	Contact Cannon Sales Department.
Weight	2 g (.086 oz.) max.