

## Product Line

DeepTronica

>

Single Pair Ethernet

>

ZConnect

>

Ceres

>

X-Lok

>

Accessory

Middle Size

Mini Size

Large Size

Standard Size

M Series

>

FLOS & FLOS+

>

Power

>

RBL

>

HS-Lok

>

NMEA 2000

>

Heavy Duty Shielded

>

RJ

>

USB

>

SSL

>

HDMI

>

DVI

>

Fiber Optic

>

RF

>

Cable Joiner

>

Cable Gland

>

Pressure Relief Vent

>

LED Light Guide

>

D-Sub

>



## ASSP-10-F-A-C-RE

Operating Temperature: N/A

Transmission Speed: N/A

Shielded: Phosphor Bronze

Jacket Material: N/A

Certificate: N/A

You must login first for view the price

Quantity

-

1

+

Check Stock

Add to Cart

Inquiry



Can't find? [Customize your part](#)

## Mating Pair & Accessories

Connector Type

Search

X-Lok, Standard...  
AB-BB02HL-BBBL  
-20°C ~ +80°C

- 0 +

☐

X-Lok, Standard...  
AB-BB02HL-BBBL  
-20°C ~ +105°C

- 0 +

☐

X-Lok, Standard...  
AB-BB02HL-BBBL  
-20°C ~ +105°C

- 0 +

☐

X-Lok, Standard...  
AB-BB02HL-BBBL  
-20°C ~ +105°C

- 0 +

☐

X-Lok, Standard...  
AB-BB02HL-BBBL  
-20°C ~ +105°C

- 0 +

☐

X-Lok, Standard...  
AB-BB02HL-BBBL  
-20°C ~ +105°C

- 0 +

☐

Add to Cart

Inquiry

Specifications	Download / CAD
Nominal Current <b>10A</b>	Connector Type <b>Terminal</b>
Shielded <b>Phosphor Bronze</b>	No. of Contacts <b>N/A</b>
Connector Gender <b>N/A</b>	Backshell <b>N/A</b>
Mating Style <b>N/A</b>	IP Rating <b>N/A</b>
Assembly Style <b>Crimp</b>	
<div><div></div>More Options</div>	

## People Also Bought

ASSP-10-F-A-C-RE

M12A04ML-12AML-...

ACC-03AFFM-SL7A01

CB-03AFMM-RL8010

BD-06BMMMA-QL8LP0

ABOUT AMPHENOL LTW

SUPPORT

PARTNERS

DOWNLOAD CENTER

FEEDBACK

Downloaded from [Arrow.com](#)