

ASSMANN
components

deutsch | english

Search:



The company | **Products** | Articlefinder | Contacts | Distribution | Download | Service

Connectors

- Customer specific solutions
- D SUB
- D SUB cover
- D SUB accessories
- DVI
- Centronics
- IDC
- Modular
- USB
- IEEE 1394
- Switches
- Power supply
- DIN 41612
- DIN 41617
- Mini DIN
- IC Socket
- **Pin and female header**
- Jumper
- Connector sleeves
- Solder terminals
- Test terminals
- Terminal Blocks
- Memory Card connectors
- FFC / FPC connectors
- Micro-Miniature



Pin and female header

AWL254-DG-G18A
female-header 02pins SMT 2,00mm 2A single row straight Au

Article number: ABL200 E G G 02 M P 1

product group: pin-&female-header

style: female-header

contact type: SMT

pin count: 2

spacing in mm: 2,00

current rating: 2A

version: single row

contact direction: straight

plating: Au

contact machining: stamped contacts

packaging: tube

process: SMT

insulator: PA6T UL94V-0

: AWL254-DG-G18A

: #NV

» PDF download «

Thermal management

Cable assembly



