

BU-P3770-@
(Gold-plated Tellurium Binding Post)



- The BU-P3770 is a panel mountable gold-plated tellurium binding post that accepts unshrouded or retractable 4mm banana plugs, bare wire, or spade lugs.
- Overall length 1.78" (45.2mm), OD = 0.44" (11.2mm)
- Mounting: Mount thru panels between 0.70" and 0.25" thick with a $\varnothing 0.375$ " (9.52mm) hole.
- Material: Contacts Gold-plated tellurium
 Insulators Polycarbonate
- Rating: Current 15 Amps
 Voltage Hands-free testing up to 2500 VRMS
 Temperature -50°C to 115°C
- Color: The "@" in the model number represents color. Available colors:
 -0 Black, -2 Red, -4 Yellow, -5 Green, -6 Blue, -9 White
- RoHS 3 compliant, exemption 6c