

5/8-24 UNEF-2A

5/8-24 UNEF-2A

15.00 [.591]

24.50 [.965]

30.30 [1.194]

7.40 [.292]

3.00 [.118]

2.10 [.083]

19.00 [.749]

14.45 [.569]

Downloaded from Arrow.com.