

3-Slot Power Cord, NEMA 5-15P to C5 - Laptop/Notebook, 10A, 125V, 18 AWG, 10 ft. (3.05 m), Black

MODEL NUMBER: **P013-010**



Laptop power cord connects your notebook or laptop with a 3-slot C6 power inlet to an AC outlet.

Features

Laptop Power Cable Connects Notebook Computers to an AC Outlet This NEMA 5-15P to C5 power cord is designed for connecting a notebook computer, laptop or other device with a three-slot C6 inlet to an AC wall outlet, surge protector, UPS system or PDU. It also powers some portable projectors, desktop computers and LG LCD televisions. The 10-ft. (3.05 m) length allows you great flexibility in placing equipment with respect to the power outlet.

Specifications

OVERVIEW	
UPC Code	037332180667
Device Compatibility	Laptop; Computer; Projector; Monitor/HDTV; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	10
Voltage Compatibility (VAC)	125
PHYSICAL	
Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC

Highlights

- Recommended for powering notebook computers and laptops with C6 inlets
- 10-ft. (3.05 m) length allows great flexibility in placing devices in relationship to AC outlet
- Ideal replacement for a worn-out or missing laptop power cable

Applications

- Connect a laptop or notebook computer to a surge protector up to 10-ft. (3.05 m) away in your workstation
- Extend an existing power connection up to 10-ft. (3.05 m) to more easily place a device or reach a power source
- Provide a high-quality replacement for a worn-out or missing laptop power cord

Package Includes

- P013-010 3-Slot Power Cord, NEMA 5-15P to C5 - 10-ft. (3.05 m), Black

Cable Jacket Rating	VW-1
Power Cord Jacket Type	SVT
Cable Outer Diameter (OD)	6.3mm
Number of Conductors	3
Wire Gauge (AWG)	18
Wire Gauge (OD - mm ²)	0.82
Cable Length (ft.)	10
Cable Length (m)	3.05
Shipping Dimensions (hwd / in.)	12.80 x 8.86 x 0.50
Shipping Dimensions (hwd / cm)	32.51 x 22.50 x 1.27
Shipping Weight (lbs.)	0.68
Shipping Weight (kg)	0.31
ENVIRONMENTAL	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	10% to 65% RH
Storage Humidity Range	10% to 65% RH
CONNECTIONS	
Side A - Connector 1	NEMA 5-15P
Side B - Connector 1	IEC-320-C5
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	No
Locking Plug	No
Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



1000 Eaton Boulevard
Cleveland, OH 44122
United States



© 2023 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.