


Series
DSXNONENVIRONMENTAL SIZE 5 CRIMP COAX PIN CONTACT
FOR RG174, RG179, RG188, RG316, KX22, FILOTEX,
122715, ASNE 0690 AND CAC875 CABLESIssue:
Dec. 04, 2013Page
1/1**MATERIAL :**

OUTER CONTACT : BRASS PER ASTM B 16 OR ASTM B 453 OR EN 12164
INSULATOR : PTFE PER ASTM-D-1710 OR EQUIVALENT
CENTER CONTACT : BERYLLIUM COPPER PER ASTM-B-196
FERRULE: BRASS PER ASTM B 16 OR ASTM B 453 OR EN 12164
CRIMP BARREL: BRASS PER ASTM B 16 OR ASTM B 453 OR EN 12164

FINISH:

ALL METALIC PARTS: .00005 OF GOLD PER SAE AMS-2422 OVER NICKEL PER AMS 2403


DESIGN REQUIREMENTS :

TEMPERATURE RANGE: -65°C to +125°C
IMPEDANCE : 50 OHMS NOMINALE
DIELECTRIC WITHSTANDING VOLTAGE: 750 V rms AT SEA LEVEL
VSWR: 1.3 from DC TO 1500 MHz

EXTRACTION TOOL: RADIAL 282 946 (M81659/28-01) (MUST BE ORDER SEPARATLY)

WIRING INSTRUCTIONS PER : RP 7575

DIMENSIONS : mm (inch are given for information only)



Estimated weight : 3.30 g

CREATION

PEN: /

NOM: /

DATE: June. 21, 1989

APPR.:

Dec. 04, 13	Updated and add CAC875 cable	Moutault	Dupuis
Sep. 24, 09	REDRAWN - SUPPRESS DETAIL OF WIRING INSTRUCTION UPDATED - ADDED WIRING INSTRUCTION RP7575	VALGRESY	BROCHET
Issue	Revisions	Name	Approved

616122EN

RADIAL PROPRIETARY INFORMATION