

Part Number : [1300950136](#)

Product Description : Heavy Duty Wire Mesh Pulling Grip, Double Weave, Rotating Eye, Standard Mesh Length 0.838m (33.00"), Approximate Break Strength 7438.92kg (16400 lbs)

Series Number : 130095

Status : Not Recommended For New Design

Product Category : Cable Grips

Engineering Part Number : 35881



Documents and Resources

Drawings

[1300950136_sd.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Not Recommended For New Design
Category	Cable Grips
Series	130095
Description	Heavy Duty Wire Mesh Pulling Grip, Double Weave, Rotating Eye, Standard Mesh Length 0.838m (33.00"), Approximate Break Strength 7438.92kg (16400 lbs)
Product Name	Heavy Duty
Type	Pulling Grip
UPC	78678835881

Agency

CSA	LR32159
-----	---------

Physical

Approximate Break Strength	7438.92kg (16400 lbs)
Bale Length	N/A
Body Style	Straight
Cable Diameter	25.40-37.85mm (1.000-1.490")
Color - Grommet	N/A
Eye Diameter	1 3/8"
Eye Type	Rotating
Gender	N/A
Material - Body	N/A
Material - Grip	Galvanized Steel
Mesh Length	0.838m (33.00")
Net Weight	1222.923/g
Number of Holes	N/A
O-Ring	N/A
Thread Size	N/A