

Representative Image

## Catalog No. GSC149

**Description: 2-PC OUTER SLV CONN PUR I.D. 0.149**

**UPC No 786210813790**

**Home > Connectivity & Grounding > Sta-Kon > Electrical terminals**

Two Piece Outer Sleeve Connector for Hexagonal Range, Length 1/4 Inch/6.4mm, Inner Diameter .149 Inches/3.78mm, Outer Diameter .179 Inches/4.54mm, Color Purple, Soft Bronze, Tin Plated

### Descriptors

| | |
|---|---|
| Category | Electrical terminals |
| Special Features | Shielded cable grounding system made of 2 cylindrical sleeves (inner sleeve + outer sleeve), for solderless crimp connection. Outer sleeve for the Hexagonal Range (the outer sleeve is crimped with a hand tool and the result is a hexagonal-shaped crimp), for grounding shielded and coaxial cables. The sleeves are color coded according to their size. Millions of installations in communications, aerospace, electronic, telephone, radio and TV applications. |

### Specifications

| | |
|---|---|
| Material | Soft Bronze |
| Color | Purple |

### Classifications

| | |
|---|---|
| Brand Name | Sta-Kon |
| Sub Brand | Shield-Kon |

### Compliance and Certifications

| | |
|---|---|
| RoHS | RoHS3 Compliant |
| REACH | REACH 240 Compliant |
| TSCA | TSCA Section 6(h) Compliant |

| | |
|---|---|
| ETIM | EC002650 Connection for screened wires |
| Model | 2-part |
| Sleeve form | Outer sleeve |
| Insulated | N |
| Outer diameter sleeve | 4.54 mm |
| Inner diameter sleeve | 3.78 mm |
| Sleeve length | 6.4 mm |
| Sleeve length | 0.25 inch |



Downloaded from Arrow.com.

| | |
|---|---|
| ETIM | EC002650 Connection for screened wires |
| Compression shape | Round |
| Reel packaging | N |



Downloaded from Arrow.com.