

Amphenol® RF


PRODUCTS

AMPHENOL RF PART NUMBER

031-8110-1

TNC Straight Clamp Plug for RG-174, RG-187, RG-188, RG-179/A, 50 Ohm

Amphenol® RF



PRODUCT IMAGE
COMING SOON

FIND STOCK & BUY NOW

ADD TO COMPARE

ADD TO PART LIST

PRODUCT OVERVIEW

RF Connector, TNC Straight Clamp Plug for RG-174, RG-187, RG-188, RG-179/A, 50 Ohm

Product Type	Connectors
Product Series	TNC
Status	Active

DOWNLOADS

Please [contact us](#) for additional product information.

PRODUCT SPECIFICATIONS

Brand	Amphenol RF
Gender	Plug
Orientation	Straight
Termination Style	Cable - Clamp
Impedance (Ohms)	50
Body Finish	Silver
Body Material	Brass
Contact Finish	Gold
Contact Material	Brass
Contact Termination Style	Solder
Insulator Material	PTFE
Cable Group	B1
Cable Type	Belden 9221, M17/94-RG179, RG-179, RG-179A, RG-179B, RG-187, RG-187A
Coupling Mechanism	Threaded
Max Frequency (GHz)	3
Polarity	Standard
Thread Direction	Standard
Min. Temp. (Celsius)	-65
Max. Temp. (Celsius)	165
Mating Cycles	500

PRODUCT COMPLIANCE

Product compliance documentation, if available is listed below:

RoHS 2 (EU)	Compliant with Exemption 6C - View Certificate
-------------	--

Additional compliance information is available in our [Product Compliance Center](#).

FOLLOW US

NEWSLETTER

AMPHENOL RF

QUICK LINKS

CONTACT US