OMRON Industrial Automation



R89F-DS1238H

DC Axial fan, plastic blade, frame 120x38, high speed

Downloaded from Arrow.com.

Specifications

Size	120 x 120 x 38 mm
Operating voltage at DC	20.4-27.6 V
Rated current	0.5 A
Rated power	12 VA
Rated rotational speed	3600 r/min
Maximum flow rate	3.88 m³/min
Maximum static pressure	135 Pa
Noise emission	49 dB(A)
Set content	Fan only

Downloads

CAD Library



R89F

Datasheet

EN PDF 5.37 MB



R89F Axial Fans

Brochure

EN PDF 5.68 MB

TERMS OF WEBSITE USE

This PDF document was created from the European OMRON Industrial Automation website on 6 August, 2026. Click here for terms of use.

OMRON

INDUSTRIAL AUTOMATION | INDUSTRIAL.OMRON.EU

Downloaded from Arrow.com.