





NOTE:

1.Material:

Terminal: Brass C2680-1/2H (HV120~140), T=0.2±0.02mm.

Shell: Brass, T=0.5±0.02mm.

Housing: LCP (E1301)+30% G.F. (UL94-0), Black.

2.Plating:

Terminal: Au plated on contact area (see order information), 100u" Sn plated on solder tail area,


both over 50u" min. Ni underplated overall.

Shell: Gold Flash overall.

3.Mechanical Characteristics:

Insertion force: 4.5Kgf max.

Withdrawing force: 1Kgf ~ 4Kgf.



RECOMMENDED PCB LAYOUT (TOP VIEW)
TOLERANCE: ±0.05mm

2017/04/06	Jody		Structural changes		A1			
2012/03/06	XIE		NEW DWG		A0			
DATE	DR.BY	ECN.NO.	DESCRIPTION	MARK	VER.			
-TOLERANCES- UNLESS OTHERWISE SPECIFIED			CnC Tech,LLC					
X.X	±0.25	X.X°	±3.00°	APPD:	TITLE: HDMI AF SMT 四脚SMT 带柱			
X.XX	±0.20	X.XX°	±1.00°	CHECK:				
X.XXX ±0.15	X.XXX°	±0.500°	DRAW:					
								
								
			PRODUCT NO: 2000-1-2-41 -00-BK	DATE	SCALE	UNIT	TYPE	PAGE
				2012/04/06	1:1	mm	Z	1 / 1