

Power Cords *1581C6 Series*

Features



- Both ends molded on with integral strain relief for long life.
- Cord length is 72" minimum. Some may be slightly longer.

Gallery



Part No.	Description	Amps	Volts AC	Cord Length	Cord Type	Cord Gauge	Plug Region	Plug Blade Type	Connector Type
1581C6EU	European Schuko plug	10	250	72.00	SVT	18/3	European	Schuko	IEC 320-C13
1581C6NA250	North American Nema 6-15P plug	10	250	72.00	SJT	18/3	North America	NEMA 6-15P	IEC 320-C13
1581C6NA	North American Nema 5-15P plug	10	125	72.00	SVT	18/3	North America	NEMA 5-15P	IEC 320-C13
1581C6UK	UK (BS1363) plug	10	250	72.00	SVT	18/3	UK	BS1363	IEC 320-C13
1581C6IEC	Male & Female IEC 320-C13 Jumper Cord	10	125	72.00	SVT	18/3	Universal	IEC 320-C13	IEC 320-C14

Data subject to change without notice.