

	1	2	3	4	5	6	7	8
A					RJ Ethernet Stranded Cable, 4xAWG 22/7, PVC outdoor, Cat. 5+, black			
B	RJ Ethernet Stranded Cable, 4xAWG 22/7, PVC, Cat. 5+, green				RJ Ethernet Trailing Cable, 4xAWG 22/7, PUR, Cat. 5+, green			
C								
D								
E	RJ Ethernet Standard Cable, 4xAWG 22/1, PVC, Cat. 5+, green							
F								

44	09475656052		100
43	09475656051		90
42	09475656050		80
41	09475656049		70
40	09475656048		60
39	09475656047		50
38	09475656046		40
37	09475656045		30
36	09475656044		20
35	09475656043		15
34	09475656042		10
33	09475656041		9
32	09475656040		8
31	09475656039		7
30	09475656038		6
29	09475656037		5
28	09475656036		4
27	09475656035		3
26	09475656034		2
25	09475656033		1.5
24	09475656032		1
23	09475656031		0.5
22	09475656022		100
21	09475656021		90
20	09475656020		80
19	09475656019		70
18	09475656018		60
17	09475656017		50
16	09475656016		40
15	09475656015		30
14	09475656014		20
13	09475656013		15
12	09475656012		10
11	09475656011		9
10	09475656010		8
9	09475656009		7
8	09475656008		6
7	09475656007		5
6	09475656006		4
5	09475656005		3
4	09475656004		2
3	09475656003		1.5
2	09475656002		1
1	09475656001		0.5
Cont. no.	Part no.	Type of cable	Dim. a[m]

88	09475656112		100
87	09475656111		90
86	09475656110		80
85	09475656109		70
84	09475656108		60
83	09475656107		50
82	09475656106		40
81	09475656105		30
80	09475656104		20
79	09475656103		15
78	09475656102		10
77	09475656101		9
76	09475656100		8
75	09475656099		7
74	09475656098		6
73	09475656097		5
72	09475656096		4
71	09475656095		3
70	09475656094		2
69	09475656093		1.5
68	09475656092		1
67	09475656091		0.5
66	09475656082		100
65	09475656081		90
64	09475656080		80
63	09475656079		70
62	09475656078		60
61	09475656077		50
60	09475656076		40
59	09475656075		30
58	09475656074		20
57	09475656073		15
56	09475656072		10
55	09475656071		9
54	09475656070		8
53	09475656069		7
52	09475656068		6
51	09475656067		5
50	09475656066		4
49	09475656065		3
48	09475656064		2
47	09475656063		1.5
46	09475656062		1
45	09475656061		0.5
Cont. no.	Part no.	Type of cable	Dim. a[m]

		Tech. Character.		Free size tol.		According to production drawing	
All rights reserved Department HCS - RO		Created by STOCHECIC Stochechi		Inspected by COSTEA Costea		Standardisation MUNTEANV Muntean	
HARTING Customised Solutions D-32339 Espelkamp		Title RJ Industrial Cable Assembly		Date 2019-09-04		State Final Release	
		Type TB		Number 09475656XXX		Rev. C	
						Page 2/3	

	1	2	3	4	5	6	7	8
A								
B								
C								
D	110	09475656182	HARTING PROFINET Type C, Torsional Stress Cable, 4xAWG 22/19, PUR, Cat. 5, green	100				
	109	09475656181		90				
	108	09475656180		80				
	107	09475656179		70				
	106	09475656178		60				
	105	09475656177		50				
	104	09475656176		40				
	103	09475656175		30				
	102	09475656174		20				
	101	09475656173		15				
	100	09475656172		10				
	99	09475656171		9				
	98	09475656170		8				
	97	09475656169		7				
	96	09475656168		6				
	95	09475656167		5				
	94	09475656166		4				
	93	09475656165		3				
	92	09475656164		2				
	91	09475656163		1.5				
	90	09475656162		1				
	89	09475656161		0.5				
E								
F	Cont. no.	Part no.	Type of cable	Dim. a[m]				

	All rights reserved	Tech. Character.		Free size tol.		According to production drawing	
	Department HCS - RO	Created by STOCHECIC Stocheci	Inspected by COSTEA Costea	Standardisation MUNTEANV Muntean	Date 2019-09-04	State Final Release	
HARTING Customised Solutions D-32339 Espelkamp		Title RJ Industrial Cable Assembly				Doc-Key / ECM-Nr. 100155397/UGD/006/C 500000157673	
		Type TB	Number 09475656XXX			Rev. C	Page 3/3