



RAPC722TR13X

RAPC722X TAPE & REEL 13",RoHS

● Out of stock

⚙️ Symbol, Footprint, 3D Model

Buy Now

< View More From This Family

- Specifications
- Videos
- Documents

Configuration

- Number of Conductors: 2
- Product Line: Power Jax
- Mounting Type: Panel
- Termination Style: Right Angle PC Mount
- Contact Plating: Silver
- High Temperature: Standard Temperature
- High Current: Standard Current
- Locking: Non-Locking
- Sealed: Not Sealed
- Packaging Type: Tape & Reel
- Standard Connector Type: DC Barrel Connectors
- Shunt: Shunted
- Jack-Plug Type: Jack
- PC Mount Style: Thru-Hole
- Special Feature: 13" Reel
- Center Pin Size: 2 mm

Electrical

- Contact Resistance: 0.05 Ohms
- Dielectric Withstanding Voltage: 250 Volts
- Insulation Resistance: 100 MOhms
- Voltage Rating: 24 Volts
- Current Rating: 5 Amps
- Circuit-Schematic: Single Closed

Mechanical

- Life Cycle: 5000 Cycles

Environmental

- Temperature Range: -55°C to +85°C
- Shielding: Unshielded
- Minimum Temperature: -55 C
- Maxiumum Temperature: 85 C

Compliance

- RoHS Compliant: Compliant
- REACH Compliant: Compliant
- Brand: Switchcraft

Material

- Body Material: Thermoplastic
- Contact Material: Copper Alloy
- Contact Plating Type: Silver
- Terminal Material: Copper Alloy Silver Plated
- Sleeve Material: Copper Alloy Silver Plated