




REV.	DATE	ECR NO.	DESCRIPTION
NC	06/16/09	XXXXXX	INITIAL RELEASE



RECOMMENDED
CABLE STRIPPING DIM'S



RECOMMENDED
MOUNTING HOLE



1. CRIMPED FERRULE
HEX CRIMP SIZE .213"
2. CONTACT PIN TO SOLDER
3. MAX. PANEL THICKNESS=2.4mm

8	FERRULE	BRASS	GOLD	1	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex						
7	CONTACT PIN	BRASS	GOLD	1		DRAWN	M.ZHANG							
6	HEX NUT	BRASS	GOLD	1		CHECKED			PART DESCRIPTION SMA BULKHEAD CRIMP JACK (FOR RG-58C/U, 58/U)					
5	LOCK WASHER	BRASS	GOLD	1		ISSUED								
4	GASKET	SILICONE	RED	1		SHEET	1 OF 1							
3	RING	BRASS	GOLD	1		PART NO. 132280RP								
2	INSULATOR	PTFE	NATURAL	1										
1	BODY	BRASS	GOLD	1		DWG. NO. 132280RP.DWG REV. NC SIZE A SCALE NA								
	DESCRIPTION	MATERIAL	FINISH	QTY										