





PART NUMBER
10124234-060003LF







ITEM NO.	DESCRIPTION	Q'TY
1	HOUSING, THERMOPLASTIC RESIN, UL94V-0	1
2	MATING CONTACT, HIGH CONDUCTIVITY COPPER ALLOY, TIN PLATED.	2
3	FLAT CONTACT, THROUGH HOLE PITCH=18.00mm HIGH CONDUCTIVITY COPPER ALLOY TIN PLATED	1
4	FLAT CONTACT, THROUGH HOLE PITCH=16.50mm HIGH CONDUCTIVITY COPPER ALLOY TIN PLATED	1
5	FLEXIBLE POWER WIRE, 6 AWG, UL RECONGIZED, 105°C, 600V RED INSULATION COLOR, LEGTH=90mm (INSULATION ONLY)	1
6	FLEXIBLE POWER WIRE, 6 AWG, UL RECONGIZED, 105°C, 600V BLACK INSULATION COLOR, LEGTH=90mm (INSULATION ONLY)	1
7	THERMAL SHRINKAGE TUBING, COLOR BLACK, 0.5mm THICKNESS. LENGTH 25mm MIN.	4

NOTES:

- (1) ELECTRICAL RATING: 600V, 60A
- (2) WORKING TEMPERATURE: -20~75°C
- (3) REFERENCE DOCUMENTS:
PRODUCT SPECIFICATION: FCI-GS-12-1127
PACKAGEING SPECIFICATION: FCI-GS-14-2295
- (4) ROHS COMPLIANT.



spec ref				dr	Beer Fu	2013-02-01	<div>projection</div> <div></div>	<div>MM</div> <div></div>	size	A3	scale	1:1
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Beer Fu	2013-02-01			ecn no			
				chr	Beer Fu	2013-02-01						
				appr	Beer Fu	2013-02-01				product family	-	rel level
surface <div></div>	linear	0.X	±0.30		title POWER CABLE FINAL ASSEMBLY			dwg no	10124234-060003LF		rev	A
		0.XX	±0.15									
		0.XXX	±0.05									
	angular	0°	±5°	www.fci.com	cat. no.	-	CUSTOMER			sheet 1 of 1		