




APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	2/7/08	
A		REDRAWN	8/03/09	
B		REVISED SPEC.	1/16/12	



RECOMMENDED PCB LAYOUT



SPECIFICATIONS:

Material:

Insulator: Hi-temp thermoplastic, glass reinforced,
rated UL 94V-0

Insulator color: Black

Contacts: Brass

Plating:

Gold Flash over Nickel underplate on contact area,
Tin over Copper underplate on PCB tails

Electrical:

Operating voltage: 30 VAC max

Current rating: 1 Amps max

Contact resistance: 50 Mohms max

Insulation resistance: 100 Mohms min


Dielectric withstanding voltage: 100 VAC for 1 minute

Temperature Rating:

Operating temperature: -20°C to +60°C

Environmental:

Lead free, RoHS compliant.



ADAM TECH

909 Ratway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

MINI USB, TYPE B, 5PIN, RIGHT ANGLE
PCB MOUNT

TITLE

SIZE

PART NO. MUSB-B5-S-RA-1

REV. B

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE IN INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES	
.X ± .10	Ø.X ± .10
.XX ± .020	Ø.XX ± .015
.XXX ± .015	Ø.XXX ± .010
APPROVALS	
DATE	

DRAWN	SS	2/7/08
CHECKED		
APPROVED		

REF: S0005C	SCALE: NTS	SHEET 1 OF 1
-------------	------------	--------------