



Part Number : [1301380127](#)

Product Description : Super-Safeway Portable Power Distribution Box, Feed-Thru, (6) GFCI Protected NEMA L5-20 Locking Single Receptacles, (1) NEMA L6-30 Locking Receptacle, NEMA Type 3R Rainproof

Series Number : 130138

Status : Active

Product Category : Power Distribution

Engineering Number : DY5-6G1H

Documents & Resources

Drawings

[1301380127_sd.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Part Details

General

Status	Active
Category	Power Distribution
Series	130138
Description	Super-Safeway Portable Power Distribution Box, Feed-Thru, (6) GFCI Protected NEMA L5-20 Locking Single Receptacles, (1) NEMA L6-30 Locking Receptacle, NEMA Type 3R Rainproof
Enclosure Rating	NEMA 3R
NEMA Configuration	NEMA L5-20, NEMA L6-30
Product Name	Super-Safeway
Type	Power Distribution Box
UPC	78172551242

Agency

UL	E135568
----	---------

Electrical

Current - Maximum per Contact	50.0A
GFCI	Yes
GFCI Reset	Manual
Ground Continuity Monitor	No
Open Neutral Relay	Yes
Voltage - Maximum	125V AC / 250V AC

Physical

Cord Diameter	N/A
Cord Grip Body Size	N/A
Cord Length	N/A
Cord Type	N/A

Feed-Thru	Yes
Flip Lid	Yes
Material - Housing	Rubber
Mounting Style	Portable
Net Weight	8541.000/g
Number of Receptacles	7
Packaging Type	Individual Carton
Receptacle Type	GFCI Single

This document was generated on Sep 22, 2025