



Connector Location A

Connector Location B





X
female



Loading-Plan:

1 — brown — 1
2 — white — 2
3 — blue — 3
4 — black — 4

Y
male



4.0 to 40	±1%
0.1 to 3.9	+0.04
a [m]	Tolerance

length in "1m" step	40	XXX=400
	39	XXX=390
	.	.
	.	.
	12	XXX=120
	11	XXX=110
length in "0.1m" step	10	XXX=100
	9.9	XXX=099
	9.8	XXX=098
	.	.
	.	.
	0.4	XXX=004
	0.3	XXX=003
	0.2	XXX=002
	0.1	XXX=001
Step	a [m]	XXX

- Protection level: IP67
- Temperature range: -25°C ... +80°C

PVC grey, 4x0.25mm ²	21348081481XXX
Type of cable	Part no.

		All Dimensions in mm		Tech. Character.		Free size tol.		According to production drawing	
All rights reserved Department HCS - RO		Created by COSTEA Costea		Inspected by MUNTEANV Muntean		Standardisation MUNTEANV Muntean		Date 2018-12-18	
HARTING Customised Solutions D-32339 Espelkamp		Title M8 Cable Assembly 4-poles st/st f/m						Doc-Key / ECM-Nr. 100578268/UGD/009/B 500000145065	
		Type TB		Number 21348081481XXX				Rev. B	
						Page 1/1			