



Part Number : [747630030](#)
Product Description : QSFP+ 14Gb Universal Loopback Adapter, 100 Ohms Impedance, Serial ID, 0dB
Series Number : 74763
Status : Obsolete
Product Category : High-Speed I/O Connectors
Engineering Number : 074763-0030



Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Part Details

General

Status	Obsolete
Category	High-Speed I/O Connectors
Series	74763
Description	QSFP+ 14Gb Universal Loopback Adapter, 100 Ohms Impedance, Serial ID, 0dB
Application	Module-to-Board
Component Type	Adapter
Product Name	QSFP Plus,QSFP+
Type	N/A
UPC	884982787292

Agency

UL	E107635
----	---------

Electrical

Current - Maximum per Contact	N/A
Shielded	No
Voltage - Maximum	3.3V

Physical

Boot Color	N/A
Circuits (Loaded)	N/A
Color - Resin	Blue (Light)
Flammability	94V-0
Gender	Dual
Lock to Mating Part	No
Material - Plating Mating	Nickel
Net Weight	29.174/g
Orientation	Horizontal
Packaging Type	Tray

Panel Mount	No
Pitch - Mating Interface	N/A
Polarized to Mating Part	No
Termination Interface Style	Through Hole

This document was generated on Sep 11, 2025

Obsolete