

5

4

3

2

1



D

C




B

A

Hood lower part



Hood upper part



Strain relief 1

Strain relief 2

Flathead screws

				Dat.	Name	 All Dim. in mm Orig. Size DIN A 4	D-Sub Hoods 25 Poles Shielded	Maßstab/ Scale 1:1
			Detail.	27/02/03	SH			
			Insp.					
EC01696	20/04/10	SC	Stand.			 HARTING EURL F-95972 Paris	TB 09 67 025 0573	Blatt/ Page 1 / 1
33806	26/09/06	PK						
31392	27/02/03	SH						
Mod.	Dat.	Name					Sub.	