



Part Number : [39000223](#)
Product Description : Mini-Fit Male Crimp
Terminal, Phosphor Bronze, Gold (Au), 16
AWG, Reel
Series Number : 5558
Status : Active
Product Category : Crimp Terminals
Engineering Number : 5558PBGS3
Packaging Alternative : 39000224 (Bag)




Documents & Resources

Drawings
[039000223_sd.pdf](#)
[55580001-PK-000.pdf](#)

Specifications
[55560001-AS-000.pdf](#)
[55560002-AS-000.pdf](#)
[55560002-PS-CH-000.pdf](#)
[55560002-PS-ES-000.pdf](#)
[55560002-PS-SK-000.pdf](#)
[55560008-TS-000.pdf](#)
[PS-5556-001-001.pdf](#)
[PS-5556-002-001.pdf](#)
[55560001-TS-000.pdf](#)
[55560010-TS-000.pdf](#)
[TS-5556-002-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)

EU RoHS	Compliant per EU 2015/863
---------	---------------------------

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Crimp Terminals
Series	5558
Description	Mini-Fit Male Crimp Terminal, Phosphor Bronze, Gold (Au), 16 AWG, Reel
Application	Power, Wire-to-Wire
Product Name	Mini-Fit
UPC	800753833401

Electrical

Current - Maximum per Contact	9.0A
Voltage - Maximum	600V

Physical

Durability (mating cycles max)	30
Gender	Male
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	126.914/mg

Packaging Type	Reel
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.80-3.10mm
Wire Size (AWG)	16
Wire Size mm ²	N/A

Use with Part(s)

Description	Part Number
Mini-Fit Jr. Plug Housings	<u>5559</u>
Mini-Fit BMI Dual Row Plug Housings	<u>42475</u>
Mini-Fit Jr. Dual Row Plug Housings	<u>46993</u>

Application Tooling

Global

Description	Part Number
Extraction Tool for Mini-Fit Jr. Terminals	<u>11030044</u>
Hand Crimp Tool for Mini-Fit Jr. Male and Female Crimp Terminals, 16 AWG	<u>2002182200</u>
FineAdjust Applicator for Insulation OD 2.20-2.45mm, 16 AWG	<u>639039400</u>
FineAdjust Applicator for Insulation OD 2.60-3.15mm, 16 AWG	<u>639041400</u>
FineAdjust Applicator for Insulation OD 1.80-2.20mm, 16 AWG	<u>639041500</u>
FineAdjust Crimp Applicator for Mini-Fit Crimp Terminals, 22+20, 20+20 and 22+18 AWG, UL 1007 Wires Only	<u>2037022100</u>
FineAdjust Crimp Applicator for Mini-Fit Crimp Terminals, 22+20, 20+20 and 22+18 AWG, UL 1061 Wires Only	<u>2037022200</u>

This document was generated on Mar 16, 2025