
CT30125C, Tie, 1.25" Max Bundle, 30 Lb Tensile, Natural



By Burndy
Catalog # CT30125C

Nylon UNIRAP™ Cable Tie - 30 Lb. Tensile Strength, Natural Color, 30 Lb. Tensile, 1.25" Max Bundle, 100 pack

Features

- Standard Cable Tie
- Suitable for General Use
- Most sizes are available in Natural or Black

Application

For General Purpose

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	Military Specified (Mil-Spec)
Military Spec Number	MS3367-5-9
Certification - ETL	No
Standards - Industry Standards Met	Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
Certification - UV Rated	No
UL Listed	Yes
Certification - CSA Approved	No
Certification - 94V0 Rated	N

Dimensions

Package Height	1.400 in
Package Weight	0.170 lb.
Package Length	10.600 in
Package Width	6.200 in
Dimension - L Length Overall mm	148 mm
Length	6 in
Dimension - Width mm	4 mm
Dimension - Width inch	0.14 in
Dimension - Length Overall inch	5.84 in
Dimension - Bundle Diameter Max inch	1.40 in

Force Related

Rating - Minimum Tensile Strength lbs	30

General

Tool Type	Intermediate
Military Specification	MS3367
Color	Natural
Sub Brand	UNIRAP,CABLE TIE
Series	UNIRAP™ Series
UPC	781810331804
Type	Intermediate
Material	Nylon 6/6
UPC 14 Digit GTIN	00781810331804

Logistics

Minimum Pack Quantity	100
Pallet Quantity	99999
Carton Quantity	1000

Operational

Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C

Product Assets

Catalog [English]

© 2026 Hubbell Incorporated. All rights reserved

Downloaded from Arrow.com.