

Part Number : [640160041](#)

Product Description : ServiceGrade Hand Crimp Tool for Field Repair only, for production use our PremiumGrade Tool

Series Number : 207126

Status : Active

Product Category : Crimp Presses and Crimp Hand Tools

Engineering Part Number : 5770



Documents and Resources

Tooling Specifications

[ATS-640160041-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Presses and Crimp Hand Tools
Series	207126
Description	ServiceGrade Hand Crimp Tool for Field Repair only, for production use our PremiumGrade Tool
Comments	ServiceGrade crimp hand tools are low cost ratcheting hand tools used in field repair for a limited number of terminations. If a high quality tool is required or a higher volume of terminations required, please purchase the corresponding PremiumGrade crimp hand tool. A ServiceGrade crimp tool may or may not have a terminal locator and in some case may need the locator removed to operate properly; Type: SERV GRADE
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	toolingsupport@molex.com
Product Name	ServiceGrade
Tool Type	Hand Crimp Tool
UPC	822348487745
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex

	<p>and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.</p>
--	--

Mates With / Use With

Use with Part(s)

Description	Part Number
PremiumGrade Hand Crimp Tool for Industrial Terminals, 22-10 AWG (see ATS)	<u>640017400</u>

Applicable Parts

Description	Part Number
Perma-Seal Ring Tongue Terminal for 22-18 AWG Wire, Stud Size 10 (M5), Carton	<u>191640003</u>
Perma-Seal Ring Tongue Terminal for 22-18 AWG Wire, Stud Size 1/4" (M6), Carton	<u>191640004</u>
Perma-Seal Ring Tongue Terminal for 22-18 AWG Wire, Stud Size 3/8" (M9), Carton	<u>191640005</u>
Perma-Seal Spade Tongue Terminal for 22-18 AWG Wire, Stud Size 6 (M3.5), Carton	<u>191640006</u>
Perma-Seal Spade Tongue Terminal for 22-18 AWG Wire,	<u>191640007</u>

Stud Size 8 (M4), Carton	
Perma-Seal Spade Tongue Terminal for 22-18 AWG Wire, Stud Size 10 (M5), Carton	<u>191640008</u>
Perma-Seal 3-Way Connector Assembly for 22-18 AWG Wire, Carton	<u>191640011</u>
Perma-Seal Butt Splice for 22-18 AWG Wire, Carton	<u>191640013</u>
Perma-Seal Butt Splice for 22-18 AWG Wire, Mylar Tape Carrier	<u>191640014</u>
Perma-Seal Ring Tongue Terminal for 16-14 AWG Wire, Stud Size 3/8" (M9), Carton	<u>191640020</u>
Perma-Seal Hook Tongue Terminal for 16-14 AWG Wire, Stud Size 10 (M5), Carton	<u>191640021</u>
Perma-Seal Ring Tongue Terminal for 16-14 AWG Wire, Stud Size 1/4" (M6), Carton	<u>191640026</u>
Perma-Seal Ring Tongue Terminal for 16-14 AWG Wire, Stud Size 5/16" (M8), Carton	<u>191640027</u>
Perma-Seal Spade Tongue Terminal for 16-14 AWG Wire, Stud Size 6 (M3.5), Carton	<u>191640028</u>
Perma-Seal Spade Tongue Terminal for 16-14 AWG Wire, Stud Size 8 (M4), Carton	<u>191640029</u>
Perma-Seal Spade Tongue Terminal for 16-14 AWG Wire, Stud Size 10 (M5), Carton	<u>191640030</u>
Perma-Seal Ring Tongue Terminal for 16-14 AWG Wire, Stud Size 6 (M3.5), Carton	<u>191640032</u>
Perma-Seal Ring Tongue Terminal for 16-14 AWG Wire, Stud Size 8 (M4), Carton	<u>191640033</u>
Perma-Seal Ring Tongue Terminal for 16-14 AWG Wire, Stud Size 10 (M5), Carton	<u>191640034</u>

Perma-Seal 3-Way Connector Assembly for 16-14 AWG Wire, Carton	<u>191640042</u>
Perma-Seal Step Down Butt Splice from 16/14 to 22/18 AWG Wire, Carton	<u>191640043</u>
Perma-Seal Butt Splice for 16-14 AWG Wire, Carton	<u>191640044</u>
Perma-Seal Butt Splice for 16-14 AWG Wire, Mylar Tape Carrier	<u>191640045</u>
Perma-Seal Butt Splice for 12-10 AWG Wire, Carton	<u>191640056</u>
Perma-Seal Butt Splice for 12-10 AWG Wire, Mylar Tape Carrier	<u>191640057</u>
Perma-Seal Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 1/2" (M12), Carton	<u>191640058</u>
Perma-Seal Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 6 (M3.5), Carton	<u>191640061</u>
Perma-Seal Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 8 (M4), Carton	<u>191640062</u>
Perma-Seal Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 10 (M5), Carton	<u>191640065</u>
Perma-Seal Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 1/4" (M6), Carton	<u>191640066</u>
Perma-Seal Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 5/16" (M8), Carton	<u>191640067</u>
Perma-Seal Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 3/8" (M9), Carton	<u>191640068</u>
Perma-Seal Spade Tongue Terminal for 12-10 AWG Wire, Stud Size 6 (M3.5), Carton	<u>191640069</u>
Perma-Seal Spade Tongue Terminal for 12-10 AWG Wire, Stud Size 8 (M4), Carton	<u>191640070</u>

Perma-Seal 3-Way Connector Assembly for 12-10 AWG Wire, Carton	<u>191640074</u>
Perma-Seal Step Down Butt Splice from 12/10 to 16/14 AWG Wire, Carton	<u>191640077</u>
Perma-Seal Ring Tongue Terminal for 22-18 AWG Wire, Stud Size 6 (M3.5), Carton	<u>191640085</u>
Perma-Seal Ring Tongue Terminal for 22-18 AWG Wire, Stud Size 8 (M4), Carton	<u>191640086</u>
Perma-Seal Hook Tongue Terminal for 16-14 AWG Wire, Stud Size 6 (M3.5), Carton	<u>191640141</u>
Perma-Seal Hook Tongue Terminal for 16-14 AWG Wire, Stud Size 8 (M4), Carton	<u>191640142</u>
Perma-Seal Ring Tongue Terminal for 22-18 AWG Wire, Stud Size 10 (M5), Mylar Tape Carrier	<u>191640306</u>
Perma-Seal Ring Tongue Terminal for 16-14 AWG Wire, Stud Size 3/8" (M9), Mylar Tape Carrier	<u>191640307</u>
Perma-Seal Ring Tongue Terminal for 16-14 AWG Wire, Stud Size 1/4" (M6), Mylar Tape Carrier	<u>191640308</u>
Perma-Seal Ring Tongue Terminal for 16-14 AWG Wire, Stud Size 5/16" (M8), Mylar Tape Carrier	<u>191640309</u>
Perma-Seal Ring Tongue Terminal for 16-14 AWG Wire, Stud Size 6 (M3.5), Mylar Tape Carrier	<u>191640310</u>
Perma-Seal Ring Tongue Terminal for 16-14 AWG Wire, Stud Size 8 (M4), Mylar Tape Carrier	<u>191640311</u>
Perma-Seal Ring Tongue Terminal for 16-14 AWG Wire, Stud Size 10 (M5), Mylar Tape Carrier	<u>191640312</u>
Perma-Seal Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 10 (M5), Mylar Tape Carrier	<u>191640316</u>

Perma-Seal Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 1/4" (M6), Mylar Tape Carrier	<u>191640317</u>
Perma-Seal Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 5/16" (M8), Mylar Tape Carrier	<u>191640318</u>
Perma-Seal Ring Tongue Terminal for 22-18 AWG Wire, Stud Size 8 (M4), Mylar Tape Carrier	<u>191640419</u>
Perma-Seal Ring Tongue Terminal for 22-18 AWG Wire, Stud Size 5/16" (M8), Carton	<u>191640435</u>
Perma-Seal Step Down Butt Splice from 12/10 to 16/14 AWG Wire, Mylar Tape Carrier	<u>191640582</u>
Perma-Seal Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 3/8" (M9), Mylar Tape Carrier	<u>191640857</u>
Perma-Seal Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 8 (M4), Mylar Tape Carrier	<u>191640938</u>
Perma-Seal Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 10 (M5), Mylar Tape Carrier	<u>191640939</u>
Perma-Seal Spade Tongue Terminal for 16-14 AWG Wire, Stud Size 6 (M3.5), Mylar Tape Carrier	<u>191640948</u>

This document was generated on Apr 29, 2026