


4

3



2

1

UNIT:mm



Electrical test:
1.100% short,open,miswire test
2.Conduct resistance:2 Ohm(max)
3.Insulation resistance:10Mohm(min)
4.dielectric test:DC 300V



IPCS/PE BAG

⑨	TIE	2	BLACK L=80mm
⑧	PE BAG	1/10	CLEAR SIZE:280*330*0.05mm PRINT BLACK"MADE IN CHINA"+"10PCS".
⑦	PE BAG	1	CLEAR SIZE:130*230*0.05mm PRINT BLACK"MADE IN CHINA"+"1PC".
⑥	OUT JACKET	18g	BLACK 45P PVC (MOLD NO:CH003)
⑤	FERRITE	2	CORE OD12*5.6*L20
⑤	OUT JACKET	6g	BLACK PVC-40P (MOULD NO:WM-40)
④	OUT JACKET	6g	BLACK PVC-40P
③	CABLE	1	USB2.0 UL2725 (28AWG*1P+24AWG*2C)+AEB(48B AIMg)
②	CONN	1set	USB A MALE SHELL:NICKEL PIN:G/F 3PCS TYPE INSULATOR COLOR:WHITE
①	CONN	1	MICRO USB 5P B/M SOLDER TYPE SHELL:NICKEL PIN:G/F INSULATOR COLOR:BLACK
NO.	NAME	Q'TY	SPECIFICATION

CnC Tech, LLC

Industrial Cable and Connector Technology			
DRAWN	licheng	DRAWING NO	
CHECKED		CUSTOMER	CNC
APPROVAL		ITEM NO.	102-1292-BL-00100
DECIDED		DATE	2012-12-20
VERSIONS/EDIT/TEON	A/0	PROJECTION	