



Part Number : [1301530022](#)

Product Description : Safeway In-Line Commercial GFCI, Permanent Mount, Single Phase, Manual Reset, Molded NEMA 5-15, 15A, 120V, 7.62m (25.0') Cord Length

Series Number : 130153

Status : Active

Product Category : Power Distribution

Engineering Part Number : 15050-25



Documents and Resources

Drawings

[1301530022_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power Distribution
Series	130153
Description	Safeway In-Line Commercial GFCI, Permanent Mount, Single Phase, Manual Reset, Molded NEMA 5-15, 15A, 120V, 7.62m (25.0') Cord Length
Enclosure Rating	NEMA 4
NEMA Configuration	NEMA 5-15
Product Name	Safeway
Type	GFCI Commercial Duty, Single Phase
UPC	78678828403

Agency

CSA	LR6837
UL	E66308

Electrical

Current - Maximum per Contact	15.0A
GFCI	Yes-In-line
GFCI Reset	Manual
Ground Continuity Monitor	No
Open Neutral Relay	Yes
Voltage - Maximum	120V AC

Physical

Cord Diameter	9.40mm (.370")
---------------	----------------

Cord Grip Body Size	Internal Double C-Clamp
Cord Length	7.62m (25.0')
Cord Type	14/3 SJTW
Feed-Thru	Yes
Flip Lid	No
Material - Housing	Nylon
Mounting Style	Portable
Number of Receptacles	1
Packaging Type	Bag
Receptacle Type	N/A

This document was generated on May 27, 2026